

RTA-3/4"UNF-2



Rotation adapter for HPH housings with 3/4"UNF mounting thread

Cylinder mounting thread: 1 1/16", #12 SAE Boss O-Ring

HPH mounting thread: 3/4", #8 SAE Boss O-Ring

This adapter is made for use with HPH housings with side opening(s). When you install the HPH in a cylinder, you may want to adjust the direction the opening is pointing. With this RTA you can adjust the direction 360°.



1. Install the RTA on the HPH mounting flange
2. Insert the RTA and HPH in the cylinder, turning clockwise until tight.
3. Depending on the direction of the side opening, you can now turn it back up to 1 turn to reach the desired position.
4. Turn the counter-nut clockwise to lock and tighten the seal.